





Configurable Plates - Copper / Brass

Tough Pitch Copper / Oxygen Free Copper / Chrome Copper / Brass Plates



RoHS 10

Part Number	Material
<input type="checkbox"/> CTAP	Tough Pitch Copper JIS H3100 C1100P-1/4
<input type="checkbox"/> CJAP	Oxygen Free Copper JIS H3100 C1020P-1/2
<input type="checkbox"/> CCSP	Chrome Copper JIS Z3234 Class 2
<input type="checkbox"/> C28P	Brass Plate JIS H3100 C2801P-1/4



Part Number	Type	Upper-Lower Surface Finish	0.1mm Increment		T Selectable/Configurable
			A	B	
CTAP (Tough Pitch Copper)	*L (Rolled)	L (Rolled)	6~300	6~300	5, 6, 8, 10, 12, 15, 20, 25, 30
CJAP (Oxygen Free Copper)					
CCSP (Chrome Copper)	F (Milled)	F (Milled)	16~300	6~300	3~30 (0.1mm Increment)
C28P (Brass Plate)					

* When CCSP (Chromium Copper) and L (Rolled) are selected, T15 or larger sizes are cast and wrought products.

Precision Standards

(Max. Value)

Item	Upper-Lower Surface Finish	
	L (Rolled)	F (Milled)
Parallelism (per 100mm)	-	0.02 or Less
Flatness (per 100mm)	2mm (per 1000 mm)	0.02 or Less
Perpendicularity (per 100mm)	0.02 or Less	
Circumference Chamfering	CO.1 Fine Chamfering	

Plate Thickness Tolerance

Upper-Lower Surface Finish	T					
	5	6, 8	10, 12	15, 20	25	30
L (Rolled)	±0.18	±0.23	±0.28	±0.35	±0.55	±0.66
F (Milled)	±0.05					



Part Number	Type	Upper-Lower Surface Finish
C28P	F	- 255.3 - 221.1 - 18.9



Part Number	A	B	T
C28PF	- 255.3 - 221.1 - 18.9 - CKT		

Alterations	Dimension Tolerance (Reduction)								
	<p>CKA, CKB, CKT</p>								
Code	CKA, CKB, CKT								
Spec.	<p>Improves the dimension tolerance. ±0.05 → ±0.025</p> <table border="1"> <thead> <tr> <th>Ordering Code</th> <th>Code</th> </tr> </thead> <tbody> <tr> <td>A (Length)</td> <td>CKA</td> </tr> <tr> <td>B (Width)</td> <td>CKB</td> </tr> <tr> <td>T (Plate Thickness)</td> <td>CKT</td> </tr> </tbody> </table> <p>CKA for A Dimension CKB for B Dimension CKT for T Dimension</p> <p>☺ Suitable for milling only.</p>	Ordering Code	Code	A (Length)	CKA	B (Width)	CKB	T (Plate Thickness)	CKT
Ordering Code	Code								
A (Length)	CKA								
B (Width)	CKB								
T (Plate Thickness)	CKT								