

■ **Features:** Extrusion End Caps for protecting 3 sides at corners.

■ **Three-Sided Caps for Corners**

**HFCK8-4040**

RoHS 10

⚠ The pin shape and numbers of extrusion caps may be changed to prevent caps from easily falling off. **M**Material: Polyamide

**ex** Example

<Before Mounting>

HFCK8-4040-B

<After Mounting>

⚠ Tapping on extrusion is not required.

Part Number	Color	Accessory	Applicable Extrusion *	Unit Price 1 ~ 14 pc(s).	Volume Discount Rate 15~19	20~200
HFCK8-4040	B (Black)	HFBMB5-15	8-4040			

\* For Aluminum Extrusion EFS Series, the same extrusion end caps as of HFS Series can be used.

**Ordering Example**

**Part Number**  
HFCK8-4040-B

■ **Features:** Extrusion End Caps Screw Mounting Type. Requires no alteration and excels in safety.

■ **Screw Mounted**

**HFCB8-4040** (Screw Fixing Type)      **HFCB8-4080** (Screw Fixing Type)

RoHS 10

**M**Material: Polyamide (Black, Light Gray, Yellow)

**ex** Example

<Before Mounting>

HFCB8-4040-B

<After Mounting>

⚠ Tapping on extrusion is not required.

Part Number Type	No.	Color	Unit Price	Volume Discount Rate	Applicable Extrusion *
			1 ~ 14 pc(s).	15~19	
HFCB8	4040	B (Black) S (Light Gray) Y (Yellow)			8-4040
	4080	⚠ Yellow Type is available for 4040 only.			8-4080

\* For Aluminum Extrusion EFS Series, the same extrusion end caps as of HFS Series can be used.  
⚠ Flat Head Screw is included for Screw Mount Type. (Black: HFBMB5-15, Light Gray, Yellow: SHFBS5-15)

**Ordering Example**

**Part Number**  
HFCB8-4040-S

■ **Features:** Extrusion End Caps only for GFS8-4040 and GFS8-4080. Alterations are required.

■ **Plates for High Rigidity Type**

**HFCD8-4040**      **HFCD8-4080**

RoHS 10

**M**Material: SUS304

**Ordering Example**

**Part Number**  
HFCD8-4040

⚠ Special alteration is required on cross sections of extrusions to mount extrusion end caps. (P.794)

Part Number Type	No.	Applicable Screw	Applicable Extrusion	Unit Price	Volume Discount Rate
				1 ~ 9 pc(s).	10~50
HFCD8	4040	SHFBS12-20 (Not included)	GFS8-4040		
	4080		GFS8-4080		