


Metal Blocks - Standard

Guaranteed Perpendicularity of All Angles - 0.1mm Increment



RoHS 10

Part Number	Material	Hardness
SSFB	SS400	-
SCFB	S50C	-
SCNFB	S50C Thermal Refined	25±3HRC
SCFF	SUS303	-
SCFS	SUS304	-



For SCNFB, the hardness may reduce depending on the plate thickness.
6-Surface Milled

0.1mm Increment		T: 0.1mm Increment				
A	B \ T	1.5-9.9			5.0-9.9	
		SSFB	SCFB	SCNFB	SCFF	SCFS
10.0- 60.0	10.0-60.0					
60.1-100.0						
10.0- 60.0	60.1-100.0				-	-
60.1-100.0					-	-

0.1mm Increment			T: 0.1mm Increment														
A	B \ T	10.0-20.0					20.1-30.0					30.1-40.0					
		SSFB	SCFB	SCNFB	SCFF	SCFS	SSFB	SCFB	SCNFB	SCFF	SCFS	SSFB	SCFB	SCNFB	SCFF	SCFS	
10.0- 60.0	10.0-60.0																
60.1- 100.0																	
100.1- 130.0																	
130.1- 160.0																	
160.1- 180.0																	
180.1- 200.0																	
200.1- 250.0		20.0-60.0			-												
250.1- 300.0					-												
300.1- 350.0					-												
350.1- 400.0					-												
400.1- 450.0				-													
450.1- 500.0			-														
10.0- 60.0	60.1-100.0																
60.1- 100.0																	
100.1- 130.0																	
130.1- 160.0																	
160.1- 180.0																	
180.1- 200.0																	
200.1- 250.0					-												
250.1- 300.0					-												
300.1- 350.0					-												
350.1- 400.0					-												
400.1- 450.0				-													
450.1- 500.0				-													
10.0- 60.0	100.1-130.0																
60.1- 100.0																	
100.1- 130.0																	
130.1- 160.0																	
160.1- 180.0																	
180.1- 200.0																	
200.1- 250.0					-												
250.1- 300.0					-												
300.1- 350.0					-												
350.1- 400.0					-												
400.1- 450.0				-													
450.1- 500.0				-													
10.0- 60.0	130.1-160.0																
60.1- 100.0																	
100.1- 130.0																	
130.1- 160.0																	
160.1- 180.0																	
180.1- 200.0																	
200.1- 250.0					-												
250.1- 300.0					-												
300.1- 350.0					-												
350.1- 400.0					-												
400.1- 450.0				-													
450.1- 500.0				-													
10.0- 60.0	160.1-180.0																
60.1- 100.0																	
100.1- 130.0																	
130.1- 160.0																	
160.1- 180.0																	
180.1- 200.0																	
200.1- 250.0					-												
250.1- 300.0					-												
300.1- 350.0					-												
350.1- 400.0					-												
400.1- 450.0				-													
450.1- 500.0				-													
10.0- 60.0	180.1-200.0																
60.1- 100.0																	
100.1- 130.0																	
130.1- 160.0																	
160.1- 180.0																	
180.1- 200.0																	
200.1- 250.0					-												
250.1- 300.0					-												
300.1- 350.0					-												
350.1- 400.0					-												
400.1- 450.0				-													
450.1- 500.0				-													